

ADLER Aquafix Bronze

8137 000300

Bronze powder for real metal effects for industrial and professional use

	PRODUCT DESCRIPTION
General	Bronze powder to achieve real metal effects on surfaces made of wood-based materials
Application area	 For the coating of furniture and interior finishing exposed to normal levels of stress, such as tabletops and shelves in the home, fronts and permanently visible areas, surfaces used on seating furniture and not permanently visible areas: Application areas III – IV according to ÖNORM A 1610-12.
	 Application in combination with a suitable topcoat system.
PROCESSING	
Instructions for use	 Carefully incorporate ADLER Aquafix Bronze 8137 000300 into the paint/hardener mixture by stirring without forming lumps. Stirring is best done by machine using a basket agitator.
Quantity to be added	250 parts by weight to 105 parts by weight of paint or paint/hardener mixture
Cleaning the working equipment	With water immediately after use.
	To remove dried paint residues we recommend using ADLER Aqua-Cleaner 80080 (diluted 1:1 with water).
	ORDERING INFORMATION
Size of trading unit	1 kg

02-17 ZKL 8137

FURTHER DETAILS

Durability/storage



At least 1 year in the original sealed containers.

- Immediately seal the container to prevent humidity from penetrating.
- Make sure the product is protected against moisture, direct sunlight, frost and high temperatures (above 30 °C).
- Do not store together with oxygen-rich and flammable materials.
- Do not store together with substances liable to spontaneous combustion.
- Keep away from oxidizing agents, as well as highly alkaline and highly acidic materials.

Safety-related information







Please pay attention to the associated safety data sheet. The current version can be accessed on the Internet at **www.adler-lacke.com**.

- Keep away from heat, hot surfaces, sparks, open flames and other sources of ignition. Do not smoke.
- Formation of explosive / highly flammable dust/air mixtures possible during use.
- Earth containers and equipment being filled.
- Use explosion-proof electrical equipment.
- In case of fire: Use special powder for metal fires or carbon dioxide (CO₂). Do not use water.

It is recommended to use safety gloves and safety glasses while processing.

The product is only suitable for industrial and professional use.